

# Knapstein


## FARA-132



### Oberfläche

- níquel
- negro
- bronce

## Technical details

|  |  |
|--|--|
| <b>País de la Fabricación</b>                |  Alemania |
| <b>fabricante</b>                            | Knapstein  |
| <b>diseñador</b>                             | Knapstein  |
| <b>año</b>                                   | 2022   |
| <b>protección</b>                            | IP20   |
| <b>Volumen de suministro</b>                 | LED  |
| <b>materi al</b>                             | metal  |
| <b>ajuste de altura</b>                      | altura ajustable   |
| <b>Atenuación</b>                            | control por movimientos  |
| <b>Potencia en vatios</b>                    | 62 W   |
| <b>LED</b>                                   | incluyendo   |
| <b>Indice de reproduccion cromatica</b>      | >90  |
| <b>El flujo luminoso en lm</b>               | 7.440  |
| <b>Temperatura de color en grados Kelvin</b> | 2200 - 3000 ajustable  |
| <b>Dimensiones del dosel</b>                 | Longitud 60 cm, altura 6 cm  |
| <b>reemplazo de la bombilla:</b>             | en el fabricante / en la fabrica   |
| <b>altura total</b>                          | 73 - 180 cm  |
| <b>Dimensions</b>                            | H 6,5 cm   B 1,4 cm   L 132 cm   |

## Descripción

The Knapstein FARA-132 is a pendant lamp with a length of 132 cm. The total height of the lamp can be adjusted at any time between 73 cm and 180 cm by lifting or pulling the lamp. The lamp can also be mounted at an angle. The FARA-132 pendant lamp emits its light upwards and downwards at the same time. By gesture control, the uplight and the downlight can be switched separately and dimmed continuously. In addition, the light colour for the uplight and downlight can be adjusted separately to a warmer tone via gesture control (from the colour temperature of 3,000 Kelvin warm white to 2,200 Kelvin extra warm white). All dimming and light colour settings are saved via memory function and automatically reset the next time the lamp is switched on.

The sensor area of the gesture control is located centrally at the top and bottom of the lamp. The lamp is switched on or off with a wiping hand movement in the sensor area. To dim the light, the hand must be held in the sensor area for a longer period of time. After the dimming process is finished, the lamp flickers briefly. By holding the hand in the sensor area again for a longer period of time, the desired light colour can also be set. The FARA-132 is available from Knapstein with a nickel matt, black or bronze effect finish. The series also includes lamps with a length of 92 cm, 112 cm and 152 cm. On request, FARA is also available in other lengths or finishes.