




# Knapstein

## LARA-205

### Technical details

|                                   |   |
|-----------------------------------|---|
| <b>Land van fabricage</b>         |  Duitsland |
| <b>fabrikant</b>                  | Knapstein   |
| <b>ontwerper</b>                  | Knapstein   |
| <b>bescherming</b>                | IP20  |
| <b>Omvang van de levering</b>     | LED   |
| <b>materiaal</b>                  | metaal  |
| <b>oppervlak</b>                  | nikkel  |
| <b>hoogteverstelling</b>          | hoogte verstelbaar  |
| <b>dimmen</b>                     | gebarencontrole   |
| <b>Wattage</b>                    | 60 W  |
| <b>LED</b>                        | inclusief   |
| <b>Kleurweergave-index</b>        | >90   |
| <b>Lichtstroom in lm</b>          | 7.112   |
| <b>Kleurtemperatuur in Kelvin</b> | 2.700 extra warm wit  |
| <b>bulb vervangen:</b>            | bij de fabrikant / fabriek  |
| <b>totale hoogte</b>              | 110 - 188 cm  |
| <b>Dimensions</b>                 | H 3,4 cm   B 1,6 cm   L 107 - 205 cm  |

### Omschrijving

The Knapstein Lara-205 pendant lamp can be adjusted in length between 107.4 cm and 205 cm by pulling or pushing the outer rails. The total height of the lamp can be adjusted between 110 cm and 188 cm with the stoppers on the cables. When switched on, the lamp must not be adjusted in height. To adjust the height, the sleeves at the bottom of the stoppers are pressed in, then the lamp can be pushed or pulled to the desired height. The pendant lamp has a surface in matt nickel.

The light of the Lara-205 is emitted simultaneously upwards and downwards. Via gesture control, the uplight and the downlight can be switched and dimmed separately. The sensor area for gesture control is located on the top of the middle rail. The lamp is switched on or off by wiping the hand. By holding the hand in the sensor area for a longer time, the light intensity can be adjusted continuously. The last selected light intensity is saved in the memory and automatically set the next time the light is switched on. The LARA-L205 series is also available with height adjustment by lifting or pulling the lamp. On request, the LARA is also available in other lengths or surfaces.